

LOMEGACLU150

Wandbeugel universeel



| | |
|--------------|---------------|
| Stand. Uitv. | Sendzimir |
| Mat. Opt. | Hot-Dip |
| Mat. Opt. PE | Poedercoating |

| | Max. belasting (in daN) |
|------------------|-------------------------|
| LOMEGACLU150.100 | 110 |
| LOMEGACLU150.150 | 100 |
| LOMEGACLU150.200 | 90 |
| LOMEGACLU150.250 | 80 |
| LOMEGACLU150.300 | 70 |
| LOMEGACLU150.400 | 50 |
| LOMEGACLU150.500 | 40 |
| LOMEGACLU150.600 | 30 |

| HD Artikel | ↕ mm | ↔ mm | → ← mm | ↔ mm | kg/stk | 📦 | Stock | Eenh. |
|----------------------------|---------|---------|------------|---------|--------|----|-------|-------|
| HD LOMEGACLU150.100 | 145 | 155 | | | 0,300 | 12 | X | STK |
| HD LOMEGACLU150.150 | 145 | 185 | | | 0,320 | 12 | X | STK |
| HD LOMEGACLU150.200 | 145 | 235 | | | 0,340 | 12 | X | STK |
| HD LOMEGACLU150.250 | 145 | 285 | | | 0,450 | 12 | X | STK |
| HD LOMEGACLU150.300 | 145 | 335 | | | 0,490 | 12 | X | STK |
| HD LOMEGACLU150.400 | 145 | 435 | | | 0,540 | 6 | X | STK |
| HD LOMEGACLU150.500 | 145 | 535 | | | 0,710 | 6 | X | STK |
| HD LOMEGACLU150.600 | 145 | 635 | | | 0,770 | 6 | X | STK |

Te bestellen per volle verpakking.
 Bevestiging van een kabelbaan door VM6.20.
 Bij montage gebruik maken van de VOMEGA om het samendrukken van het profiel te verhinderen.
 Max. Belasting (daN): Gelijkmatig verdeeld over de volledige breedte.

Niet te gebruiken voor VFUL30.065, VFUL35.150, VFU35.150, VFUL 60.050.